



# MATRIKX<sup>®</sup> + 10/2

## Extruded Activated Carbon Block Filter

### The Only Choice

- **3 µm Nominal Filtration**
- **>99.5% Reduction of 10 µm Particles**
- **6,000 Gallons >98% Chlorine Taste and Odor Reduction at 1.0 GPM**
- **Enhanced Dirt Holding Capacity**
- **No Release of Carbon Fines**
- **Significantly Exceeds Performance of Traditional GAC and PAC Filters**
- **High Performance at Low Cost**
- **Performance Tested and Verified by Independent Laboratory Testing**



MATRIKX<sup>®</sup> + 10/2 is the perfect choice for point-of-use (POU) and reverse osmosis systems. Because of its extremely low cost, the MATRIKX<sup>®</sup> + 10/2 is also the ideal replacement wherever GAC (granular activated carbon) or PAC (powdered activated carbon) filters are used.

The 2.50" O.D. x 9.75" length filter delivers >98% average chlorine taste and odor reduction @ 1.0 GPM for 6,000 gallons.\*\* The 2.50" O.D. x 20" length filter delivers >98% average chlorine taste and odor reduction @ 2.0 GPM for 12,000 gallons.\*\*

Manufactured using KXI patented, solid-state extrusion process, the MATRIKX<sup>®</sup> + 10/2 surpasses the performance of GAC and PAC, but is offered at an extremely competitive price. Unlike GAC/PAC filter elements, there is no channeling, fluidizing or release of carbon fines.

\*\*Based on laboratory results

### Technical Specifications and Order Information

Part No.	O.D. x Length	Weight	Chlorine Taste & Odor Reduction Capacity @ Flow	Nominal µm Rating	Initial ΔP @ Flow
10-250-190-975	2.50" x 9.75"	0.75 lbs.	>6,000 gal. @ 1.0 GPM	3 µm	2.00 psid @ 1.0 GPM
10-250-190-20	2.50" x 20"	1.75 lbs.	>12,000 gal. @ 2.0 GPM	3 µm	2.00 psid @ 2.0 GPM



## ORDER INFORMATION

Special order filters are available in varying sizes with lengths from 1" to 60".

Standard filters are finished with an outer prefiltration medium. A protective polypropylene netting is applied to the exterior of the cartridge. Polypropylene end caps with compression gaskets fit most standard housings.

Inquire concerning alternative filter finishing options, including alternative end cap and housing interface styles, a wide range of non-standard extruded filter sizes, and non-standard prefiltration systems.

## EXTRUDED CARBON = EXCEPTIONAL VALUE

MATRIKX® + 10/2 filters consist of activated carbon particles fused into a uniform block with enhanced adsorptive capacity and efficiency. MATRIKX® + 10/2 filters flow in a radial (outside-to-inside) direction, providing increased dirt-holding capacity and low pressure drop. Unlike granular activated carbon (GAC) filters, MATRIKX® + 10/2 cartridges will not channel or bypass due to the extreme uniformity of their extruded activated carbon core. Service life of the MATRIKX® + 10/2 filter is greatly extended by a layer of prefiltration medium.

- No channeling
- No fluidizing
- No bypassing
- Eliminates release of carbon fines
- Lowest extractables, pure materials of construction
- Maximum service life and resistance to fouling
- Graded density prefiltration design
- Manufactured using FDA-compliant materials

Made in the USA.

Distributed by:



## NOTES

1. Projected chlorine taste and odor reduction capacity when tested in accordance with NSF/ANSI Standard 42 protocol.
2. Nominal particulate rating (3 µm) is for >85% of a given size as determined from single-pass particle counting results.\*
3. Absolute particulate rating (10 µm) is for >99.9% of particles of a given size as determined from single-pass particle counting results.\*\*

\*Nominal Filter Rating: Filter rating indicating the approximate size particle, the majority of which will not pass through the filter. It is generally interpreted as meaning that 85% of the particles of the size equal to the nominal micron rating will be retained by the filter. (WQA Glossary of Terms, Third Edition, 3-97).

\*\*Absolute Filter Rating: Filter rating meaning that 99.9% (or essentially all) of the particles larger than a specific micron rating will be trapped on or within the filter. (WQA Glossary of Terms, Third Edition, 3-97).

## WARNINGS:

Maximum Operating Temperature:	125°F
Maximum Operating Pressure:	250 psig
Maximum Differential Pressure:	100 psid
Collapse Pressure:	200 psid

MATRIKX® filters are not to be autoclaved or steam-sterilized.

Use MATRIKX® + 10/2 carbon filters only with microbiologically safe and adequately disinfected water. Activated carbon filters are not designed to kill or remove bacteria or viruses.

Actual results obtained will vary with various combinations of organic contaminants, changes in pH or other conditions encountered in actual use.

All information presented here is based on data believed to be reliable. It is offered for evaluation and verification, but is not to be considered a warranty of any kind.

MATRIKX® filters are designed to fit most standard household and commercial or industrial housings.

Contact KX Industries, L.P. to check filter housing compatibility.

This cartridge must be placed in an appropriate housing and flushed for a minimum of 5 minutes prior to use.

### LIMITED LIABILITY

KX Industries, L.P. makes no warranties of any kind, expressed or implied, statutory or otherwise, and expressly disclaims all warranties of every kind, concerning the product, including, without limitation, warranties of merchantability and fitness for a particular purpose, except that this product should be capable of performing as described in this product's data sheet. KX Industries, L.P.'s obligation shall be limited solely to the refund of the purchase price or replacement of the product proven defective, in KX Industries, L.P.'s sole discretion. Determination of suitability of this product for uses and applications contemplated by Buyer shall be the sole responsibility of Buyer. Use of this product constitutes Buyer's acceptance of this Limited Liability.

This product is covered by one or more of the following United States Patent Nos. 5,019,311; 5,147,722; 5,189,092; 5,249,948; 5,331,037; 5,685,981; 5,922,803; 5,946,342; 6,061,384; 6,395,190; applicable foreign equivalents; and patents pending.

©2005 KX Industries, L.P. All rights reserved. KX, the KX logo, MATRIKX, and the MATRIKX GENUINE EXTRUDED CARBON seal are registered trademarks of KX Industries, L.P.

269 South Lambert Road  
Orange, CT 06477-3502  
Telephone: 203-799-9000  
Fax: 203-799-7000  
Toll Free: 800-462-8745  
E-mail: sales@kxindustries.com  
www.kxindustries.com

